

SPECIFICATION SHEET

Intelligent Bidet Toilet Seat

Newtech Code: V8214




Features

- Material: Polypropylene
- Dimensions: H90 x W375mm x D495mm
- Suitable for Casalino Toilet Only
- Heated Seat with adjustable temperature levels and warm air dryer
- Soft Close Seat
- Automatic opening/closing lid
- Adjustable Nozzle position
- IP Rating: IPX4 Class 1
- Rated Power : 820W
- Rated Voltage :220V~50Hz
- Operating Temperature : 0°C – 40°C
- Water Pressure Requirement: : 0.70-750kPa
- Power Cord Length: 1.5M
- Maximum User Weight : 120kg
- Night Light
- Overheating Protection
- Removable Toilet Seat Cover
- Water Filter (Optional)

Please note: This Bidet seat must be installed with a Reduced Pressure Zone (RPZ) Valve or other backflow prevention device, which is not supplied by Newtech. This is required to meet the Building Code requirements. Please consult with your registered Plumber.

Technical Details

Note: All measurements shown are in millimetres. Sizes are nominal.




SPECIFICATION SHEET

Bidet Remote Control

Smart remote control with display screen. The user-friendly interface and clearly labelled buttons allow for intuitive operation and effortless control of various modes

- Can be wall mounted
- Require 2x batteries (not supplied)




Controls Information

- Posterior Wash Button – Turn on cleaning for 90 seconds. Double clicking this button will turn on mobile/massage cleaning effect as water moves back and forth
- Feminine Wash Button – Turn on cleaning for 90 seconds. Double clicking this button will turn on mobile/massage cleaning
- Stop Button - Turn off any function that is active.
- Air Dry Button - turn on air drying for 180 seconds.
- Eco Mode Button – turn on and off Energy Saving Mode
- Night Light Button – turn on and off the night light. Selecting this function will allow the night light to turn on when there is no other light on in the room.
- Nozzle Mist Button – adjust the nozzle to a comfortable position (4 positions available)
- Water temperature button – adjust the water temperature up and down. (4 temperatures available – room temperature, low (35°C), medium (37°C) and high (40°C)
- Seat temperature button – adjust seat temperature up and down. (4 temperatures available – room temperature, low (35°C), medium (37°C) and high (40°C)
- Air temperature button – adjust air temperature up and down. (4 temperatures available – room temperature, low (35°C), medium (37°C) and high (40°C)
- Water Pressure button – adjust the water pressure up and down.
- Automatic Mode Button – turn automatic mode on and off. When this is selected cleaning mode will automatically turn on for 90 seconds then drying mode will automatically turn on for 180 seconds
- Self-Cleaning Button – Turn on and off the self-cleaning for the Nozzle.
- Radar Sensor Button – Turn on and off the Radar Sensor. Selecting this function will allow the radar to sense a human approaching the toilet which will open the toilet lid and then close the toilet lid when no one is in the room.
- Bubble Shield Button – Turn on and off the bubble shield. Selecting this function will allow the seat to spray bubbles around the toilet seat when you sit on the seat and when you leave the seat for a cleaner experience.
- Open/Close Lid Button – Open and Close Lid
- Open/Close Seat Button – Open and Close Seat
- LED display Screen - this screen will show all the functions that have been selected and the temperature of these functions.

SPECIFICATION SHEET

Control Knob



PRODUCT OVERVIEW

The stepless colourful control knob simplifies multiple functions for easy use without having to use the remote control.

Features

- Located left side of toilet seat
- Counterclockwise rotation – Turn on Posterior Wash and moving/massage nozzle
- Clockwise Rotation – Turn on for 90 seconds Feminine wash and moving/massage Nozzle for 90 seconds.
- Single Press – Turn off any function that is active.
- Long press while seated – Turn on drying function for 180 seconds

Different light meaning

- Green: Standby
- Red: Drying
- Purple: Feminine Wash
- Blue: Posterior Wash
- Light Blue: Sitting detected